



# Visualume Tunnel Luminaire (VLM)

Visualume, 250 HPS,

Visualume, 250 HPS,

Subtle design and simple lines makes the Visualume VLM Series a good choice for tunnels, underpasses, highway entry ways and exits as well as tollbooths. Given the harsh conditions prevailing in their intended environments, luminaires in the Visualume have been developed for physical as well as photometric performance. <a href="http://www.lumec.com/Lumec3Dv2/home/index\_en.php" target="\_blank"><b>Lumec3D: Online 3D Configurator</b></a>

## Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	250
Photometric Distribution Type	Type IV
Mounting	Surface Wall
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Square

Product Data	
Order product name	Visualume, 250 HPS,
Commercial Code	VLM-250HPS-SWA (S0000063)
Order code	VLM-250HPS-SWA (S0000063)
Catalog Number Description	Visualume, 250 HPS,
Service / Spec Smart	-
Material Nr. (12NC)	LUM10000207