



# Transit Post Top (TR10)

## Transit, 250 MH, Type III, Medium, Cutoff, Sag Lens

Transit, 250 MH, Type III, Medium, Cutoff, Sag Lens

Combining state-of-the-art photometric performance with outstanding ease-of-maintenance the decorative Transit luminaires are designed to last in even the most demanding environments. The versatility and character of the Transit luminaire is clear. Combining stunning good looks with outstanding photometric performance, the Transit incorporates the cutting edge photometrics and ease of maintenance that have made Lumec luminaires the perfect choice for effective area lighting. Equipped with the optional LifeLED the Transit's standard dark-sky friendly full cut-off optics turn this versatile product into one of the most environmentally responsible luminaires available on the market. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

### Product data

General Information	
Lamp Source Code	Metal Halide
Lamp Watts	250
Photometric Distribution Type	Type III
Mounting	Pole Top
Operating and Electrical	
Voltages	120/208/240/277/347/480 V

Mechanical and Housing	
Shape	Round
Product Data	
Order product name	Transit, 250 MH, Type III, Medium, Cutoff, Sag Lens
Order code	TR10-250MH-SCB3M
Material Nr. (12NC)	LUM70009580
Catalog Number	TR10-250MH-SCB3M
Catalog Number Description	Transit, 250 MH, Type III, Medium, Cutoff, Sag Lens

## Transit Post Top (TR10)

---

