



TR Recessed Retrofit Kit

Troffer Retrofit Kit available with 3 lamp T5, T8 or Biax.

Troffer Retrofit Kit available with 3 lamp T5, T8 or Biax.

The TR troffer retrofit kit is designed to offer the end user a cost effective way to increase the efficiency and lumen output of existing troffer fixtures. Applications include warehouse, general lighting, classrooms, gymnasiums and retail applications. TR retrofit kits are available with a variety of lamp and reflector combinations allowing the customer to design the TR system to meet or exceed existing light levels and customize the “look” to match their specific needs. Philips Optimum recommends the coupling of the Enhanced Specular reflector with high lumen T8 lamps as a way to maximize lumen output and fixture efficiency. The TR troffer retrofit is designed for easy installation in existing troffer fixtures.

Product data

General Information	
Lamp Source Code	FLU
Number of Lamps	3
Product Data	
Order product name	Troffer Retrofit Kit available with 3 lamp T5, T8 or Biax.
Commercial Code	TR D23 24 332 UV 1PS E

Order code	TR D23 24 332 UV 1PS E
Catalog Number Description	Troffer Retrofit Kit available with 3 lamp T5, T8 or Biax.
Service / Spec Smart	-
Material Nr. (12NC)	OPT00000225