## LIGHTOLIER

by (s) ignify

Calculite LED

Gen 3 Product offering





# Experience the change, see the difference

Lightolier Calculite LED generation 3 continues the legacy of forward innovation with our new reduced brightness optics. While your requirements may change, our frame doesn't have to change.

#### **Benefits**

Our three-part luminaire enables easy upgrade of technology, beam angles and color temperatures to create the impact desired in any space over the life of the building. While the requirements may change, our frame doesn't have to. This design also enables convenient servicing and upgrading of technology, beam angles and color temperatures to create the impact desired in the space over the life of the installation.

- Maximize visual appeal with three beam spread options to offer the right distribution and light output.
- 50° direct (physical) and 45° reflected (optical) cut offs ensure proper positioning of optics and light source.
- Installation efficiency accomplished by a tool-free installation using quick connect technology.
- Adjustable springs accommodate ceiling thicknesses up to 2" (4" aperture) and 2.75" (6" & 7" apertures).
- Standard dimming to 1% for 0-10V. ELV, Lutron, Dali, POE & TW.
- Uniform light and color consistency at an SDCM of 2.
- Lowest plenum height in tool-free 50° cutoff downlight.











# Gen 3 Calculite LED

### downlighting product offering

#### **Features**

Apertures: 4", 6" & 7" Rounds, 4" & 6" Squares, 4" & 6" Cylinders. Flanges: Polished, White, Black & Flangeless available in all sizes. Frames: Future proof, no electronics (most versatile frame available). Light Engines: Modular design (easy to upgrade and replace components).

Reflectors: Available in six different finish options in all sizes.

Beam Spreads: Narrow, Medium and Wide available in all lumen ranges.

Lifetimes/Efficacies: Up to L90 at 60,000 hrs. with efficacies up to 115 lm/W.

Note: Refer to specification sheets for downlight beam spread angles, wet locations and ENERGY STAR® configurations. The 7in downlight offers up to five beam spread options (please refer to 7in downlight specification sheet for details).

**Quiet Zone** No Visible elements: Lens, Clips, Rivets, Rings or other hardware Transition Zone 50° Direct View Cut Off **Bright Zone** 45° Reflected View Cut Off

#### **Downlights**

201111191112											
	13/4" 3" 4"		4"	6"	7"	1×1"	4x4" 6x6"				
	very narrow to medium beams					very narrow to medium beams					
	12° 17° 25° 38° 47°	N M W	N M W	N M W	N M W	12° 17° 25° 38° 47°	N M W N M W				
Lumens											
400	• • • • •										
500			• • •								
1000		• • •	• • •	• • •	• • •						
1500			• • •	• • •	• • •						
2000			• • •	• • •	• • •						
2500			• • •	• • •	• • •						
3000			• • •								
3500				• • •	• • •						
4800				• • •	• • •						
6000				• • •	• • •						

#### Adjustable Accents

Adjust	able Accella	•
	3"	4"
	12° 16° 19° 26° 40°	11° 17° 22° 29°
Lumens		
400		
500		
1000	• • • • •	
1500		• • • •
2000		
2500		
3000		
3500		
4800		
6000		

#### **Wall Washers**

	13/4"	3"		4	"			6	5"	)		7	7"	)		4x4"	6x	:6"
Lumens	LW	LW	LW	ww	DW	CW	LW	ww	DW	CW	LW	ww	DW	CW	-	LW	LV	N
400 500 1000	•	•	•	•	•	•	•	•	•	•	•	•	•	•	-			
1500 2000 2500			• • •	•	•	•	•	•	•	•	•	•	•	•		-		
3000 3500 4800 6000			•	•	•	•		•	•	•		•	•	•		•		•
回接器原	] vi	isit Sign	ify.cc	m/w	arrar	nties	N	= Narr	ow be	eam	<b>M</b> = Me	edium	beam	W =	Wic	le beam	LW =	Lensed

#### Cylinders

	4"				6"		4"	6"		
	(									
	N	М	W	N	М	W				
Lumens							ww	ww		
400										
500	•	•	•				•			
1000	•	•	•	•	•	•	•	•		
1500	•	•	•	•	•	•	•	•		
2000	•	•	•	•	•	•	•	•		
2500	•	•	•	•	•	•	•	•		
3000	•	•	•				•			
3500				•	•	•		•		
4800				•	•	•		•		
6000				•	•	•		•		



for more information on Signify's standard 5-year limited warranty.

ed Wall Wash **WW** = Wall Wash **DW** = Double Wall Wash **CW** = Corner Wall Wash

See Calculite LED specification sheets for additional drawings and technical information.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

