

**PHILIPS**



Garage & Canopy

SoftView



# Parking **with confidence**

Philips Gardco SoftView LED parking garage luminaires use indirect illumination and uplight to reduce glare and eliminate the cave effect so that your patrons can feel comfortably secure. Utilizing LED technology reduces energy and maintenance costs compared to conventional technologies, and savings are further enhanced through a variety of dimming and control options.



## Features and benefits

- Edge lit technology creates soft, uniform illumination that increases visual comfort without compromising performance or exposing viewers to harsh glare
- Uplight directed onto the ceiling eliminates cave effect
- Achieves up to 124 LPW for lower energy costs even during constant operation
- A variety of lumen packages available, with output ranging from approximately 2200 - 10600 lumens
- Four distribution patterns are available to create your ideal parking garage environment
- Cool, neutral, and warm white color temperatures
- Long LED life reduces maintenance time and expenses compared to conventional technologies
- Added flexibility and further enhance savings through optional controls, including 0-10V dimming, motion response and Wireless controls

## Ordering guide

example: SVPG-140L-2100-NW-G2-SM-5-UNV-BL-IMRI2-MGY

Luminaire	Number of LEDs	Drive Current	Color Temperature	Mounting	Distribution	Emergency	Voltage	Options			Finish
								Dimming controls	Motion sensing	Electrical	
<b>SVPG</b>	<b>140L</b>										
SVPG SoftView Parking Garage	140L 140 LEDs (comfort engine)	450 450mA 800 800mA 1200 1200mA 1675 1675mA 2100 2100mA	WW-G2 Warm White 3000K (70 CRI) Generation 2 NW-G2 Neutral White 4000K (70 CRI) Generation 2 CW-G2 Cool White 5000K (70 CRI) Generation 2 WY-G2 Warm Yellow 2700K (80 CRI) Generation 2 BW-G2 Balanced White 3500K (80 CRI) Generation 2	SM Surface / Pendant Mount (pendant and junction box by others) T Trunnion Mount (ordered separately, see Accessories) WM Wall Mount (ordered separately, see Accessories)	1R Type IR Rectangular 3 Type III Asymmetric 5 Type V CD Concentrated Downlight	NONE Leave Blank EBP Emergency Battery pack EBPC Emergency Battery pack cold rated	120 120V 208 208V 240 240V 277 277V UNV Universal 120-277V 347 347V 480 480V HVV Universal 347-480V	NONE Leave Blank DD 0-10V Dimming external leads (controls by others) BL Bi-level with motion sensor LLC Wireless Controls	NONE Leave Blank IMRI2 Integral Motion Response, #2 lens IMRI3 Integral Motion Response, #3 lens  (factory customizable, contact factory)	Fusing F1 Single Fuse (120, 277, 347V) F2 Double Fuse (208, 240, 480V) F3 Double Fuse Canadian double pull (208, 240, 480V) Surge Protection blank SP1 10KV 5KA (standard) SP2 20KV 10KA (option)	BZ Bronze MGY Medium Gray WH White OC Optional Color Specify optional color or RAL ex: OC-LGP or OC-RAL7024. SC Special Color Must supply color chip. Requires factory quote.



(contact factory for WY-G2 or BW-G2)

## Accessories (ordered separately)

**FSIR-100** Hand-held programmer (For use with 'IMRI2' and 'IMRI3' motion response when field programming is required). If desired, only one is needed per job.

**ES** External House Side Shield (field installed)

**SVPG-G2-TM-(F)** Trunnion Mount kit (field installed)

**SVPG-G2-WM-(F)** Wall Mount (field installed)

(F) = specify finish

**BXC** Bird excluding coil (field installed, fits on all mounting options)

**BXK** Bird excluding spikes (field installed, fits on Pendant, Trunnion, and Wall mounts only)

**BXS** Bird excluding shroud (field installed, fits on Pendant mount only)

Prior to ordering, consult specification sheets on [philips.com/luminaires](http://philips.com/luminaires) for the most current information, notes, and exclusions.

© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. [philips.com/luminaires](http://philips.com/luminaires)



Philips Lighting North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008