



PHILIPS  
DuraMax  
Incandescent Reflector  
Wide Flood  
65W  
Medium Base  
Clear

Lighting Facts/Datos de Iluminación	
Per Bulb/Per Bombilla	
Brightness/Brillo	625 lumens/lúmenes
Estimated Yearly Energy Cost/ Costo Estimado Anual de Energía	\$7.83
Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use./Basado en 3 hrs/día, 11¢/kWh. Costo depende de la tarifa y el uso.	
Life/Duración	2.3 years/años
Based on 3 hrs/day/Basado en 3 hrs/día	
Light Appearance/Apariencia de Iluminación	
Warm/Cálida 2740 K Cool/Fría	
Energy Used/Usó de Energía	65 watts/vatios

046677167820



# Brighten your home with infinite possibilities

Philips 65W Duramax wide reflector flood incandescent long life bulb is ideal for use in indoor recessed lighting. This 65W bulb emits a soft white and creating an ambient light effect that lasts 2.3 years\* with an estimate cost of \$7.83\*\*

#### Dimmable

- Dimmable

#### Ambiant light effect

- Offers a wide beam of ambient light

#### Instant on

- Instant on

# PHILIPS

# Highlights

## Dimmable

This bulb can be used with most dimmers to create your desired ambience.

## Wide beam of ambient light

This reflector flood provides a wide beam of light ideal for use in kitchens, hallways and family rooms. It offers a downlight specifically made for recessed ceiling and track fixtures

## Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

# Specifications

## Bulb characteristics

- Shape: Reflector
- Dimmable: No
- Base: Medium Base
- Lamp shape code: BR40

## Bulb dimensions

- Width: 5 inch
- Height: 6.5 inch

## Durability

- Average life (at 2.7 hrs/day): 2.3 year(s)
- Nominal lifetime: 2,500 hour(s)

## Light characteristics

- Application: Accent light, Basic light
- Beam angle: 60 degree(s)
- Color rendering index (CRI): 100
- Color temperature: 2700 K
- Light Color Category: Soft White, Frosted
- Nominal luminous flux: 625 lumen
- Starting time: 0 s
- Warm-up time to 60% light: Instant full light

## Power consumption

- Power consumption per 1000h: 7.82925 kW
- Voltage: 120 V
- Wattage: 65 W

## Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677167820
- EAN/UPC - Case: 50046677167412
- SAP Gross Weight EAN (Piece): 0.176 kg
- Net Weight (Piece): 0.001 kg
- SAP Height (Piece): 18.415 cm
- SAP Length (Piece): 12.382 cm
- SAP Width (Piece): 12.382 cm



Issue date: 2019-05-01  
Version: 0.270

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)