

# PHILIPS

Incandescent  
Reflector Flood

Incandescent

65W

Medium Base

Clear

## Lighting Facts/Datos de Iluminación

Per Bulb/Por Bombilla

**Brightness/Brillo** 620 lumens/lúmenes

**Estimated Yearly Energy Cost/Costo Estimado Anual de Energía** \$7.83


Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use./Basado en 3 hrs/día, 11¢/kWh. Costo depende de la tarifa y el uso.

**Life/Duración** 2.3 years/años

Based on 3 hrs/day/Basado en 3 hrs/día

**Light Appearance/Apariencia de Iluminación**

Warm/Cálida Cool/Fría



**Energy Used/Usos de Energía** 65 watts/vatios

046677225193



## Brighten your home with infinite possibilities

Philips 65W standard reflector flood incandescent bulb is ideal for use in your indoor recessed lighting. This 65W bulb emits a soft white light, creating an ambient light effect that lasts 1.8 years\* with an estimated cost \$7.83\*\*.

### Dimmable

- Dimmable

### Ambiant light effect

- Offers a wide beam of ambient light

### Instant on

- Instant on

# Highlights

## Dimmable

This bulb can be used with most dimmers to create your desired ambience.

## Wide beam of ambient light

This reflector flood provides a wide beam of light ideal for use in kitchens, hallways and family rooms. It offers a downlight specifically made for recessed ceiling and track fixtures

## Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

# Specifications

## Bulb characteristics

- Shape: Reflector
- Dimmable: No
- Base: Medium Base
- Lamp shape code: BR30

## Bulb dimensions

- Width: 3.75 inch
- Height: 5.37 inch

## Durability

- Average life (at 2.7 hrs/day): 1.8 year(s)
- Nominal lifetime: 2,000 hour(s)

## Light characteristics

- Application: Accent light, Basic light
- Beam angle: 55 degree(s)
- Color rendering index (CRI): 100
- Color temperature: 2700 K
- Light Color Category: Soft White, Frosted
- Nominal luminous flux: 620 lumen
- Starting time: 0 s
- Warm-up time to 60% light: Instant full light

## Power consumption

- Voltage: 120 V
- Wattage: 65 W

## Bulb characteristics

- Shape: Reflector
- Application: Accent light, Basic light
- EAN/UPC - product: 046677225193
- Average life (at 2.7 hrs/day): 1.8 year(s)
- Beam angle: 55 degree(s)
- Net weight: 0.052 kg
- Gross weight: 0.070 kg
- Color rendering index (CRI): 100
- Height: 14.605 cm
- Color temperature: 2700 K
- Length: 9.525 cm
- Width: 3.75 inch
- Light Color Category: Soft White, Frosted
- Width: 9.525 cm
- Voltage: 120 V
- Height: 5.37 inch
- Nominal luminous flux: 620 lumen
- Wattage: 65 W
- Base: Medium Base
- Starting time: 0 s
- Lamp shape code: BR30
- Warm-up time to 60% light: Instant full light



Issue date: 2022-05-11  
Version: 0.552

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)