



PHILIPS
EnergySaver
Linear Compact
Fluorescent
7W
PL-S
G23; 2-Pin Base

046677230227

Energy savings and long life

Philips Compact Fluorescent light bulbs offer significant energy savings, great light output and a wide variety of shapes and sizes.

Ease of use

- Designed for use with magnetic ballasts

Light effect

- Provides a comfortable and relaxing environment

Sustainable choice

- Reduced mercury for an environmentally friendly alternative

Perfect Shape

- For use in recessed and surface mounted downlight fixtures

PHILIPS

Highlights

For use with existing ballasts
Soft white light

ALTO Lamp Technology
For general lighting use

Specifications

Bulb characteristics

- Intended use: Indoor

Light characteristics

- Application: Comfortable light, Soft light

Power consumption

- Wattage: 7 W

Technical specifications

- Lamp holder: PL-S
- Number of lamps: 1
- Placement: Recessed can

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677230227
- EAN/UPC - Case: 50046677230222
- SAP Gross Weight EAN (Piece): 44.400 g
- Net Weight (Piece): 26.000 g
- SAP Height (Piece): 19.500 cm
- SAP Length (Piece): 3.600 cm
- SAP Width (Piece): 8.900 cm



Issue date: 2019-09-08
Version: 0.268

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com