

PHILIPS

Metal Halide

HID

175W

ED28

Mogul Base

046677253592



Many models for indoor and outdoor applications

Philips High Intensity Discharge light bulbs offer unbeatable light quality and consistent performance.

Premium quality

- Provides dusk-to-dawn lighting in outdoor security fixtures

Highlights

For Outdoor use

Specifications

Bulb characteristics

- Intended use: Indoor, Outdoor
- Bulb Finish: Clear
- Bulb Material: Hard Glass

Light characteristics

- Application: Special application
- Color rendering index (CRI): 65
- Correlated Color Temperature (Nom): 4000
- Luminous Efficacy (rated) (Nom): 84 lm/W

Power consumption

- Wattage: 175 W

Technical specifications

- Lamp holder: ED28
- Number of lamps: 1
- Placement: Ceiling fixtures, Outdoor Security
- Chromaticity Coordinate Y: 0.400
- Chromaticity Coordinate X: 0.375
- Cap-Base: E39 | Single Contact Mogul Screw

Packaging dimensions and weight

- EAN/UPC – product: 046677253592
- Net weight: 0 kg
- Gross weight: 0.31 kg
- Height: 23.6 cm
- Length: 10.4 cm
- Width: 10.4 cm
- Material number (12NC): 928601150312



Issue date: 2024-02-04
Version: 0.534

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com