

PHILIPS

Metal Halide

HID

400W

ED28

Mogul Base

046677253677



Many models for indoor and outdoor applications

Philips High Intensity Discharge light bulbs offer unbeatable light quality and consistent performance.

Premium quality

- Provides dusk-to-dawn lighting in outdoor security fixtures

Highlights

For Outdoor use

Specifications

Bulb characteristics

- Intended use: Indoor, Outdoor

Light characteristics

- Application: Special application

Power consumption

- Wattage: 400 W

Technical specifications

- Lamp holder: ED28
- Number of lamps: 1
- Placement: Ceiling fixtures, Outdoor Security



Issue date: 2023-11-08
Version: 0.534

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com