

PHILIPS

Ceramalux High
Pressure Sodium

HID

70W

ED23 1/2

Mogul Base

046677253783



Many models for indoor and outdoor applications

Philips High Intensity Discharge light bulbs offer unbeatable light quality and consistent performance.

Premium quality

- For indoor general lighting and outdoor security fixtures

Highlights

Indoor and outdoor use

Specifications

Bulb characteristics

- Intended use: Indoor, Outdoor

Light characteristics

- Application: Special application

Power consumption

- Wattage: 70 W

Technical specifications

- Lamp holder: ED23.5
- Number of lamps: 1
- Placement: Ceiling fixtures, Outdoor Security

Packaging dimensions and weight

- EAN/UPC - product: 046677253783
- Net weight: 18.000 g
- Gross weight: 109.000 g
- Height: 21.000 cm
- Length: 9.100 cm
- Width: 9.100 cm
- Material number (12NC): 928601139906
- Net Weight: 18.000 g
- SAP Height (Piece): 21.000 cm
- SAP Length (Piece): 9.100 cm



Issue date: 2020-06-03
Version: 0.532

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com