



PHILIPS
Indoor Spot Light
40W
R16
Medium Base

046677415402

Light for all of your specialized fixtures

Philips Specialty Incandescent and halogen bulbs provide the perfect light for accent and display lighting as well as general lighting in a variety of applications.

Perfect Shape

- Ideal for recessed cans and track light fixtures

Specialty bulb

- Ideal for cabinet and display lighting

PHILIPS

Highlights

For indoor spot light fixtures

Compact spot light

Specifications

Bulb characteristics

- Intended use: Indoor

Light characteristics

- Application: Accent light

Power consumption

- Voltage: 120 V
- Wattage: 40 W

Technical specifications

- Lamp holder: R16
- Number of lamps: 1
- Placement: Cabinets, Displays, Recessed cans, Track light

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677415402
- EAN/UPC - Case: 50046677415407
- SAP Gross Weight EAN (Piece): 0.082 kg
- Net Weight (Piece): 0.081 kg
- SAP Height (Piece): 17.780 cm
- SAP Length (Piece): 10.160 cm
- SAP Width (Piece): 5.080 cm



Issue date: 2019-04-01
Version: 0.268

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com