

PHILIPS

Appliance

40W

T8

Intermediate Base

046677416256



Light for all of your specialized fixtures

Philips Specialty Incandescent and halogen bulbs provide the perfect light for accent and display lighting as well as general lighting in a variety of applications.

Specialty bulb

- For microwaves, ovens, sewing machines, and other appliances

Highlights

For household appliances

Specifications

Characteristics

- Intended use: Indoor

Light characteristics

- Application: Special application

Power consumption

- Voltage: 130 V
- Wattage: 40 W

Technical specifications

- Lamp holder: T8
- Number of lamps: 1
- Placement: Microwave, Oven, Sewing Machines

Packaging dimensions and weight

- EAN/UPC – product: 046677416256
- Net weight: 0.007 kg
- Gross weight: 0.013 kg
- Height: 12.700 cm
- Length: 7.938 cm
- Width: 2.591 cm
- Material number (12NC): 925164536103



Issue date: 2023-11-08
Version: 0.534

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com