

# PHILIPS

## Reflector

Halogen

50W

GU5.3

Sparkling light

Dimmable

**Lighting Facts** Per Bulb,  
**Brightness** 850 lumens, **Estimated Yearly Energy Cost** \$6.02 (Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use), **Life** 2.7 years (Based on 3 hrs/day), **Energy Used** 50 watts, **Light Appearance** 3000 K

Suitable for both indoor and outdoor-landscape fixtures

Apropiado tanto para accesorios de paisajismo interiores como exteriores

**CAUTION: THIS LAMP IS PRESSURIZED AND COULD SHATTER** so to avoid injury and to avoid exposure to ultraviolet radiation, this lamp should be used in a fixture that provides a protective shield of tempered glass. Provide adequate ventilation to ensure that seal temperature does not exceed 350°C and use only in fixtures rated for the wattage stated on this package. To avoid risks of burns or other injury, turn power off and allow lamp to fully cool before attempting to replace. Socket condition may affect lamp life. Inspect and replace socket if deterioration has occurred.

**PRECAUCIÓN: ESTA BOMBILLA ESTÁ PRESURIZADA Y PODRÍA ESTRELLARSE**, esta bombilla deberá de usarse en un accesorio que ofrezca un escudo protector de vidrio templado, para evitar lesiones y evitar exponerse a

046677419332



## Brilliant alternative to incandescents

Philips 50W dimmable halogen indoor and outdoor flood provides bright, sparkling accent light. An efficient alternative to a 50W incandescent, it has no mercury, can last up to 2.7 years\* and has an estimated yearly energy cost of \$6.02\*\*.

### Easy to use

- Dimmable
- Instant On

### Sparkling light

- Bright alternative to incandescent



# Highlights

## Dimmable

This bulb can be used with most dimmers to create your desired ambience.

## Alternative to incandescent

This halogen light bulb provides a bright, sparkling light, ideal for adding brilliance and drama to your home.

## Instant On



Just by turning the switch, the light is at full brightness. No slow starting or waiting.

# Specifications

## Bulb characteristics

- Shape: Mini Reflector Flood
- Dimmable: Yes
- Base: GU5.3
- Lamp shape code: MRC16

## Bulb dimensions

- Height: 44.4 mm
- Width: 50.8 mm

## Durability

- Average life (at 2.7 hrs/day): 2.7 year(s)
- Nominal lifetime: 3,000,000 hour(s)

## Light characteristics

- Application: Accent light
- Color rendering index (CRI): 100
- Color temperature: 3000 K
- Light Color Category: Clear
- Nominal luminous flux: 750 lumen

## Power consumption

- Voltage: 12 V
- Wattage: 50 W

## Packaging dimensions and weight

- EAN/UPC - product: 046677419332
- Net weight: 0.032 kg
- Gross weight: 0.038 kg
- Height: 12.700 cm
- Length: 4.550 cm
- Width: 7.620 cm
- Material number (12NC): 924888417102



Issue date: 2020-10-26  
Version: 0.531

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)