

PHILIPS

Bulb (Dimmable)

LED

10W (65W)

E26

Warm Glow

Dimmable

046677457020



The right light makes the moment

The Philips LED WarmGlow lamps offer a new experience for dimmable LEDs, by enabling light levels to dim to the warm tones of traditional lamps. You can change the ambience from functional lighting to an inviting and cozy atmosphere.

Create a warm atmosphere

- Dims to a warm glow

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Long life bulbs – Lasts up to 25 years

Highlights

WarmGlow dimming



With this dimmable bulb, you can dim from a 2700k warm light to a 2200K light. The more you dim, the warmer the light.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

Specifications

Characteristics

- Shape: Bulb
- Dimmable: Yes
- Lamp shape: Non directional reflector
- Socket: E26
- Lamp shape code: BR40

Bulb dimensions

- Height: 16 cm
- Width: 12.5 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2200–2700 K
- Light Color Category: Warm Glow, Warm White
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 120 mA

Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 65 W

Product dimensions & weight

- Length: 16 cm

Rated values

- Rated beam angle: 110 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 10 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 046677457020
- Net weight: 0.142 kg
- Gross weight: 0.185 kg
- Height: 22.400 cm
- Length: 12.700 cm
- Width: 18.700 cm
- Material number (12NC): 929002009135



Issue date: 2023-11-07
Version: 0.476

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com