



PHILIPS
LED
Candle (Dimmable)
4.5W (40W)
E26
Soft White
Dimmable



046677461928



Light that's easy on your eyes

Poor quality light could cause eye strain. It's more important than ever to properly light your home. Philips LED lamps fulfill stringent test criteria to ensure they meet our Eyecomfort requirements†

Long life

- Long Life

Modern Style

- Modern lighting in Philips LED

Energy savings

- Energy savings

Add a beautiful sparkle to your home

- Decorative bulb

PHILIPS

Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes
- No visible flicker

Highlights

Long Life



Reduce the hassle of replacing bulbs so often

Modern lighting

Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips and post lights.

Energy saving

Enjoy the energy-savings of LEDs without sacrificing light quality

Decorative bulb

With its clear, elegant design and innovative LED technology, this decorative bulb produces a warm, sparkling light effect, adding a touch of tranquillity to your home atmosphere.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Specifications

Bulb characteristics

- Shape: B11
- Dimmable: Yes
- Base: E26

Bulb dimensions

- Width: 1.42 inch
- Height: 4.13 inch

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 300 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 43 mA
- Mercury content: 0 mg

Power consumption

- Power consumption per 1000h: 5 kW
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 4.5 W
- Wattage equivalent: 40 W

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 300 lumen
- Rated power: 4.5 W

Packaging dimensions & weight

- EAN/UPC - Case: 50046677461923
- SAP Gross Weight EAN (Piece): 0.000 kg
- Net Weight (Piece): 0.030 kg
- SAP Length (Piece): 0.000
- SAP Width (Piece): 0.000
- SAP EAN/UPC - Set: 046677461928



Issue date: 2019-09-18
Version: 0.277

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com