

PHILIPS

Bulb

LED

13.5W-100W

E26

Daylight



046677462000



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Long life bulb - Lasts up to 10 years

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

Designed for the comfort of your eyes



glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

Specifications

Bulb characteristics

- Shape: Bulb
- Dimmable: Non Dimmable
- Intended use: Indoor
- Lamp shape: Bulb
- Socket: E26
- Type of glass: Frosted
- Base: E26
- Lamp shape code: A19
- Control: On/off switch

Bulb dimensions

- Width: 2.4 inch
- Height: 4.21 inch

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 10,950 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 1500 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 228 mA

Power consumption

- Power factor: 0.5
- Voltage: 120 V
- Wattage: 14 W
- Wattage equivalent: 100 W

Product dimensions & weight

- Length: 10.7 cm

Rated values

- Rated lifetime: 10,950 hour(s)
- Rated luminous flux: 1500 lumen
- Rated power: 14 W

Technical specifications

- Frequency: 60 Hz

Bulb characteristics**[12.5A19/LED/850/FR/P/ND 4/2FB]**

- Application: Task lighting
- EAN/UPC - product: 046677462000
- Rated beam angle: 150
- Height: 11 cm
- Average life (at 2.7 hrs/day): 11 year(s)
- Beam angle: 150
- Lamp current: 220 mA
- Net weight: 0.084 kg
- Rated lifetime: 11,000 hour(s)
- Intended use: Indoor
- Weight: 0.06 kg
- Lumen maintenance factor: 70%
- Color consistency: 6 SDCM
- Gross weight: 0.109 kg
- EAN: 046677462000
- Rated luminous flux: 1500 lumen
- Lamp shape: Bulb
- Width: 6 cm
- Color rendering index (CRI): 80
- Height: 10.700 cm
- EOC: 462002
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 5000 K
- EyeComfort: Yes
- Length: 6.200 cm
- Product title:
12.5A19/LED/850/FR/P/ND 4/2FB
- Power factor: 0.5
- Rated power: 12.5 W
- Technology: LED
- Light Color Category: Daylight
- Width: 10.000 cm
- Voltage: 120 V
- Type of glass: Frosted
- Nominal luminous flux: 1500 lumen
- Material number (12NC):
929001958203
- Wattage: 12.5 W
- Length: 11 cm
- Starting time: 0.5 s
- Wattage equivalent: 100 W
- Lamp shape code: A19
- Warm-up time to 60% light: Instant full light
- Control: On/off switch

- Frequency: 60 Hz

Bulb characteristics**[13.5A19/LED/850/FR/P/ND 4/2FB]**

- EAN/UPC - product: 046677462000
- Height: 11.7 cm
- Average life (at 2.7 hrs/day): 11 year(s)
- Lamp current: 255 mA
- Net weight: 0.100 kg
- Rated lifetime: 11,000 hour(s)
- Intended use: Indoor
- Weight: 0.049 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.128 kg
- EAN: 046677462000
- Rated luminous flux: 1500 lumen
- Lamp shape: Non directional bulb
- Width: 6 cm
- Color rendering index (CRI): 80
- Height: 11.500 cm
- EOC: 462002
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 5000 K
- EyeComfort: Yes
- Length: 6.200 cm
- Product title:
13.5A19/LED/850/FR/P/ND 4/2FB
- Power factor: 0.5
- Rated power: 13.5 W
- Technology: LED
- Light Color Category: Daylight
- Width: 10.000 cm
- Voltage: 120 V
- Type of glass: Frosted
- Nominal luminous flux: 1500 lumen
- Material number (12NC):
929002311803
- Wattage: 13.5 W
- Length: 11.7 cm
- Starting time: <0.5 s
- Wattage equivalent: 100 W
- Warm-up time to 60% light: Instant full light
- Color Code: 850 | CCT of 5000K
- Frequency: 60 Hz



Issue date: 2022-06-12
Version: 0.494

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.