

# PHILIPS

Candle (Dimmable)

LED

4.5W (40W)

E26

Daylight

Dimmable



046677463922



## Light that's easy on your eyes

Poor quality light could cause eye strain. It's more important than ever to properly light your home. Philips LED lamps fulfill stringent test criteria to ensure they meet our Eyecomfort requirements†

### Long life

- Long Life

### High quality light

- Designed for the comfort of your eyes
- No visible flicker

### Modern Style

- Modern lighting in Philips LED

### Energy savings

- Energy savings

### Add a beautiful sparkle to your home

- Decorative bulb

# Highlights

## Long Life



Reduce the hassle of replacing bulbs so often

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## Modern lighting

Modern lighting in Philips LED candles for use in decorative fixtures such as in chandeliers, ceiling fans, vanity strips and post lights.

## Energy saving

Enjoy the energy-savings of LEDs without sacrificing light quality

## Decorative bulb

With its clear, elegant design and innovative LED technology, this decorative bulb produces a warm, sparkling light effect, adding a touch of tranquillity to your home atmosphere.

# Specifications

## Characteristics

- Shape: B11
- Dimmable: Yes
- Base: E26

## Bulb dimensions

- Width: 1.42 inch
- Height: 4.13 inch

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 300 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 43 mA

#### Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 4.5 W
- Wattage equivalent: 40 W

#### Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 300 lumen
- Rated power: 4.5 W

#### Packaging dimensions and weight

- EAN/UPC – product: 046677463922
- Net weight: 0.090 kg
- Gross weight: 0.116 kg
- Height: 11.300 cm
- Length: 3.700 cm
- Width: 11.100 cm
- Material number (12NC):  
929001213103



Issue date: 2023-11-08  
Version: 0.528

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)