

PHILIPS

Bulb

LED

9.5W - 8W - 3W (60W)

Medium Screw base

Daylight/Soft White/Warm
Glow

Non-dimmable



046677464868



One bulb, 3 color settings

With Philips SceneSwitch LED bulbs, you can switch light settings without switching bulbs. Flip your existing switch to change from soft white light, to daylight, to a cozy warm glow. No dimmer or additional installation is required.

Application areas

- Application

Long life

- Long Life

Energy efficient

- Energy savings

High quality light

- Designed for the comfort of your eyes

SceneSwitch

- SceneSwitch

Color settings

- Color settings

Highlights

Application

Ideal for any room in your home.

Long Life

With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs. Philips LED bulbs enable the perfect lighting solution for over 13 years.

Energy saving

Enjoy the energy-savings of LEDs without sacrificing light quality

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

SceneSwitch

All-in-one replacement bulb that gives you three different light settings.

Color settings

Flip from soft white to daylight to a cozy warm glow, all with your existing switch.

Specifications

Characteristics

- Shape: A19, Bulb
- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Base: Medium Screw base

Bulb dimensions

- Width: 2.4 inch
- Height: 4.3 inch

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Soft light
- Color rendering index (CRI): 80
- Color temperature: 2700-5000-2200 K
- Light Color Category: Color Change
- Nominal luminous flux: 800-800-80 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 130 mA

Packaging information

- Product family: SceneSwitch

Power consumption

- Energy Star Certified: No
- Power factor: 0.62
- Voltage: 120 V
- Wattage: 9.5, 8, 3 W
- Wattage equivalent: 60 W

Product dimensions & weight

- Length: 11.1 cm

Rated values

- Rated power: 9.5 W

Technical specifications

- Frequency: 60 Hz



Issue date: 2023-11-08
Version: 0.533

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com