



PHILIPS
Hue White ambiance
Light recipe kit E26
1 x E26 bulb
Warm to cool white light
Easy access to light
scenes
Dimmer switch included

046677466701

Helps you to read, relax, concentrate and energize

Get started with the Philips Hue Light Recipe Kit. With the included E26 bulb and dimmer switch, you can cycle through four preset light recipes and enjoy wireless dimming. Connect everything to the Hue bridge to unlock the smart features.

Limitless possibilities

- Use smart lights to sharpen your focus
- Get energized in cool white light
- Read in the right smart light
- Relax with warm white smart lights
- Expand to a smart light system with the Hue Bridge
- Wireless control with included dimmer switch

PHILIPS

Highlights

Sharpen your focus



The cool white light of the preset Concentrate light recipe allows you to focus on the task at hand, whether you're helping your kids with homework or getting your own work done.

Get energized



The preset Energize light recipe is a cool, bright white that gets your energy levels up in the morning, letting you start your day off right.

Read in the right smart light




The preset Read light recipe tunes the light to just the right shade and intensity to ensure that you can read your book, magazine, or newspaper comfortably.

Relax with warm white light



The soft yellow glow of the preset Relax light recipe allows you to calm your mind and body. Use this light recipe when you need to unwind and sleep better at night.

Expand with Hue Bridge



When connected to a Hue Bridge (*sold separately), your smart lights become even more versatile. Control your lights from anywhere inside and outside your home using just the Philips Hue app. Set timers, routines, and add or remove lights from your system.

Wireless control



With the battery-powered dimmer switch, you can control up to 10 smart lights simultaneously. The switch • which can be removed from its wall mount and used as a remote control • allows you to dim and brighten your lights or cycle through four preset light recipes

Specifications

Also tested on

- Android: Yes
- Google Nexus: Yes
- HTC: Yes
- Motorola Nexus: Yes
- Note: Yes
- OnePlus: No
- Samsung Galaxy: Yes
- Sony: No

Environmental

- Operational humidity: 5% <H<95% (non condensing)
- Operational temperature: -10°C – 45°C

Guarantee

- 3 years: Yes

The bulb

- Color temperature: 2200K-6500K
- Diameter: 62 mm
- Fitting: E26
- Form factor: A19
- Height: 109 mm
- Input voltage: 110V-130V
- Lifetime: 25,000 hour(s)
- Light output: Warm white to cool daylight
- Lumen output: 800 lm @ 4000K
- Max. operation power: 10 W
- Max. standby power: 0,1 W
- Software upgradable: when connected to Hue bridge
- Start up: Instant 100% light output
- Wattage: 10 W
- Diameter: 2.4 inch
- Height: 4.3 inch

What's in the box

- Bridge: No
- Ethernet network cable: No
- Hue bulbs: No
- Hue dimmer switch: 1
- Hue Tap switch: No
- Hue white bulbs: No
- Power adapter: No
- Tone bulbs: 1

What's supported

- HomeKit compatible: Yes
- IOS: Yes
- iPad: Yes
- iPad Air: No
- iPad Mini: No
- iPhone: Yes
- iPod Touch: No

Logistical information: Philips Hue WA LRK 10W A19 E26 US

- SAP EAN/UPC – Piece: 046677466701
- EAN/UPC – Case: 50046677466706
- SAP Gross Weight EAN (Piece): 0.292 kg
- Net Weight (Piece): 0.180 kg
- SAP Height (Piece): 16.500 cm
- SAP Length (Piece): 7.500 cm
- SAP Width (Piece): 17.600 cm



Issue date: 2019-04-01
Version: 0.219

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com