



PHILIPS  
LED  
Spot (Dimmable)  
4W-50W  
GU10  
Bright White Light  
Dimming

046677468118

## Dimmable LED light with a focused bright beam

Philips dimmable LED GU10 spot light bulbs are a long lasting, energy efficient replacement for halogen spots. They have a bright white light and are ideal for accent lighting in recessed, track, and decorative fixtures.

### High quality light

- Designed for the comfort of your eyes
- Bright white light

### Light beyond illumination

- Dimmable
- Instant on

# PHILIPS

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go

easy on the eyes, and create the perfect ambience for your home.

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambience to host friends or wind down with a book.

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Instant on

# Specifications

## Bulb characteristics

- Shape: Spot
- Dimmable: Yes
- Socket: GU10

## Bulb dimensions

- Height: 5.3 cm
- Width: 5 cm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 35 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 400 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 40 mA
- Mercury content: 0 mg

## Power consumption

- Power factor: 0.85
- Voltage: 120 V
- Wattage: 4.5 W
- Wattage equivalent: 50 W

## Rated values

- Rated beam angle: 35 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 400 lumen
- Rated peak intensity: 750 cd
- Rated power: 4.5 W

## Packaging dimensions & weight

### [BC4.5GU10/LEDCLA/3000/F35 Dim 120V]

- SAP EAN/UPC - Piece: 046677468118
- EAN/UPC - Case: 50046677468113
- SAP Gross Weight EAN (Piece): 0.072 kg
- Net Weight: 0.046 kg
- SAP Height (Piece): 20.400 cm
- SAP Length (Piece): 5.100 cm
- SAP Width (Piece): 12.000 cm

**Packaging dimensions & weight**  
**[4GU10/LED/930/F35/DIM/G/120V**  
**4/1BC]**

- SAP EAN/UPC - Piece: 046677468118
- EAN/UPC - Case: 50046677468113
- SAP Gross Weight EAN (Piece): 0.074 kg
- Net Weight: 0.056 kg
- SAP Height (Piece): 15.400 cm
- SAP Length (Piece): 5.200 cm
- SAP Width (Piece): 12.500 cm



Issue date: 2019-11-28  
Version: 0.412

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)