

PHILIPS

Reflector

LED

13.5 W

E26

Non-dimmable



046677469078



Bright LED lighting with excellent light quality

Philips LEDspots are a perfect replacement for your halogen spot: they deliver halogen-like light and performance that you expect from the LED technology.

High quality light

- Designed for the comfort of your eyes

Instant on

- Instant on

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Choose for a sustainable solution

- No UV or InfraRed

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Specifications

Bulb characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor, Outdoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Type of glass: Blue
- Lamp shape code: PAR38
- Control: On/off switch

Bulb dimensions

- Height: 13.2 cm
- Width: 12.2 cm

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Nominal lifetime: 10,950 hour(s)
- Number of switch cycles: 10,000

Light characteristics

- Application: Task lighting, Accent lighting
- Color rendering index (CRI): 80
- Light Color Category: Blue
- Nominal luminous flux: 200 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 165 mA
- Efficacy: 80 lm/W

Packaging information

- Product family: Party

Power consumption

- Power factor: 0.5
- Voltage: 120 V
- Wattage: 13.5 W

Product dimensions & weight

- Length: 13.2 cm

Rated values

- Rated beam angle: 100 degree(s)
- Rated lifetime: 10,950 hour(s)
- Rated peak intensity: 520 cd
- Rated power: 13.5 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 046677469078
- Net weight: 0.385 kg
- Gross weight: 0.482 kg
- Height: 13.700 cm
- Length: 12.500 cm
- Width: 12.500 cm
- Material number (12NC): 929001306513



Issue date: 2023-11-08
Version: 0.486

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com