

# PHILIPS

Reflector

LED

13.5 W

E26

Non-dimmable



046677469108



## Bright LED lighting with excellent light quality

Philips LEDspots are a perfect replacement for your halogen spot: they deliver halogen-like light and performance that you expect from the LED technology.

### High quality light

- Designed for the comfort of your eyes

### Instant on

- Instant on

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

### Choose for a sustainable solution

- No UV or InfraRed

# Highlights

## Gentle LEDs, easy on the eyes




It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

## Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

# Specifications

## Bulb characteristics

- Dimmable: Non Dimmable
- Intended use: Indoor, Outdoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Type of glass: Red
- Lamp shape code: PAR38
- Control: On/off switch

## Bulb dimensions

- Height: 13.2 cm
- Width: 12.2 cm

## Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Nominal lifetime: 10,950 hour(s)
- Number of switch cycles: 10,000

## Light characteristics

- Application: Task lighting, Accent lighting
- Color rendering index (CRI): 80
- Light Color Category: Red
- Nominal luminous flux: 900 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

**Miscellaneous**

- EyeComfort: Yes

**Other characteristics**

- Lamp current: 165 mA
- Efficacy: 75 lm/W

**Packaging information**

- Product family: Party

**Power consumption**

- Power factor: 0.5
- Voltage: 120 V
- Wattage: 13.5 W

**Product dimensions & weight**

- Length: 120 cm

**Rated values**

- Rated beam angle: 60 degree(s)
- Rated lifetime: 10,950 hour(s)
- Rated peak intensity: 600 cd
- Rated power: 13.5 W

**Technical specifications**

- Frequency: 50 Hz

**Bulb characteristics**

- Application: Task lighting, Accent lighting
- EAN/UPC - product: 046677469108
- Rated beam angle: 60 degree(s)
- Height: 13.2 cm
- Average life (at 2.7 hrs/day): 11 year(s)
- Lamp current: 165 mA
- Net weight: 0.385 kg
- Product family: Party
- Rated lifetime: 10,950 hour(s)
- Intended use: Indoor, Outdoor
- Gross weight: 0.482 kg
- Lamp shape: Reflector
- Width: 12.2 cm
- Color rendering index (CRI): 80
- Height: 13.700 cm
- Rated peak intensity: 600 cd
- Socket: E26
- Number of switch cycles: 10,000
- EyeComfort: Yes
- Length: 12.500 cm
- Power factor: 0.5
- Rated power: 13.5 W
- Technology: LED
- Light Color Category: Red
- Width: 12.500 cm
- Voltage: 120 V
- Type of glass: Red
- Nominal luminous flux: 900 lumen
- Wattage: 13.5 W
- Length: 120 cm
- Starting time: <0.5 s
- Lamp shape code: PAR38
- Warm-up time to 60% light: Instant full light
- Control: On/off switch
- Frequency: 50 Hz



Issue date: 2022-05-11  
Version: 0.486

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)