

# PHILIPS

Linear tube

LED

7W (17W)

G13

Daylight

Non-dimmable



046677469436



## Bright LED lighting with excellent light quality

This Philips LED linear tube provides an exceptionally long life and significant energy savings. With its bright color temperature, this tube is the perfect long-lasting replacement for your linear fluorescent (TL) tubes.

### High quality light

- Designed for the comfort of your eyes
- Cool, day light

### Plug and Play

- Plug and play

### Choose a simple replacement for your old bulbs

- Perfect replacement T8 linear fluorescent application

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Cool, day light



This bulb has a color temperature of 6500K, and is the highest color temperature available in this bulb category. It therefore gives you a lighting effect that is the closest to that of natural daylight. This will help you focus and experience every detail.

## Plug and play

Simple and quick do-it-yourself project with no wiring required and no need to replace your existing ballast.\*\*\*

## Similar to linear fluorescents

The perfect quick and easy replacement for T8 linear fluorescent tubes. It fits directly into standard T8 linear fluorescent G13 sockets.

# Specifications

## Characteristics

- Shape: Tube
- Dimmable: Non Dimmable
- Intended use: Indoor
- Lamp shape: Linear tube
- Socket: G13
- Lamp shape code: T8
- Control: On/off switch

## Bulb dimensions

- Height: 60.28 cm
- Width: 2.63 cm

## Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 0.7
- Number of switch cycles: 5,000

## Light characteristics

- Application: Task lighting
- Color consistency: 6 SDCM
- Color rendering index (CRI): 82
- Color temperature: 6500 K
- Light Color Category: Daylight
- Nominal luminous flux: 1150 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 80-240 mA

## Packaging information

- Product family: InstantFit

## Power consumption

- Power factor: >0.9
- Voltage: 120 - 277 V
- Wattage: 7 W
- Wattage equivalent: 17 W

## Rated values

- Rated lifetime: 5,000 hour(s)
- Rated luminous flux: 1150 lumen
- Rated power: 7 W



Issue date: 2023-11-08  
Version: 0.813

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)