



PHILIPS
LED
Linear tube
7W (17W)
G13
Cool White

046677469443

LED task lighting with excellent light quality

InstantFit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. They provide a natural lighting effect for use in general lighting applications, as well as instant energy savings.

Instant on

- Instant light when switched on

Choose for high quality light

- Cool, white light

Choose a simple replacement for your old bulbs

- No UV or InfraRed

PHILIPS

Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes

Highlights

Instant On



No need to wait: Philips LED light bulbs provide their full level of brightness immediately when they are switched on. Just by flipping the switch, your room is at full brightness. There is no slow starting or waiting.

No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

Specifications

Bulb characteristics

- Shape: Tube
- Dimmable: No
- Socket: G13

Bulb dimensions

- Height: 602.8 mm
- Width: 26.3 mm

Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 50,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Color rendering index (CRI): 82
- Color temperature: 4000 K
- Light Color Category: Cool White
- Nominal luminous flux: 1150 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 80-240 mA
- Mercury content: 0 mg

Power consumption

- Power factor: >0.9
- Voltage: 120 - 277V, 347 V
- Wattage: 7 W
- Wattage equivalent: 17 W

Rated values

- Rated lifetime: 50,000 hour(s)
- Rated luminous flux: 1150 lumen
- Rated power: 7 W

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677469443
- EAN/UPC - Case: 50046677469448
- SAP Gross Weight EAN (Piece): 0.146 kg
- Net Weight (Piece): 0.120 kg
- SAP Height (Piece): 2.800 cm
- SAP Length (Piece): 61.600 cm
- SAP Width (Piece): 2.800 cm



Issue date: 2019-04-22
Version: 0.271

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com