

PHILIPS

Linear tube

LED

9W (25W)


G13

Cool White

Non-dimmable



046677469450



Bright LED lighting with excellent light quality

This Philips LED linear tube provides an exceptionally long life and significant energy savings. With its bright color temperature, this tube is the perfect long-lasting replacement for your linear fluorescent (TL) tubes.

High quality light

- Designed for the comfort of your eyes

Plug and Play

- Plug and play

Choose for high quality light

- Cool, white light (4000K)

Choose a simple replacement for your old bulbs

- Perfect replacement T8 linear fluorescent application

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Similar to linear fluorescents

The perfect quick and easy replacement for T8 linear fluorescent tubes. It fits directly into standard T8 linear fluorescent G13 sockets.

Plug and play

Simple and quick do-it-yourself project with no wiring required and no need to replace your existing ballast.****

4000K [LED Lamps]

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

Specifications

Bulb characteristics

- Shape: Tube
- Dimmable: Non Dimmable
- Intended use: Indoor
- Lamp shape: Linear tube
- Socket: G13
- Lamp shape code: T8
- Control: On/off switch

Bulb dimensions

- Height: 90.76 cm
- Width: 2.63 cm

Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 0.7
- Number of switch cycles: 5,000

Light characteristics

- Application: Task lighting
- Color consistency: 6 SDCM
- Color rendering index (CRI): 82
- Color temperature: 4000 K
- Light Color Category: Cool White
- Nominal luminous flux: 1200 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 60-180 mA
- Mercury content: 0 mg

Packaging information

- Product family: InstantFit

Power consumption

- Power factor: >0.9
- Voltage: 120 - 277 V
- Wattage: 9 W
- Wattage equivalent: 25 W

Rated values

- Rated lifetime: 5,000 hour(s)
- Rated luminous flux: 1200 lumen
- Rated power: 9 W



Issue date: 2020-06-04
Version: 0.774

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com