

PHILIPS
LED
Bulb (Dimmable)
8W-60W
E26
Warm Glow
Dimming

046677469740



The right light makes the moment

Philips LEDs with a dimmable warm glow effect, enables light levels to dim to the warm tones of traditional bulbs. You can change the ambience from functional lighting to an inviting and cozy atmosphere.

Create a warm atmosphere

- Dims to a warm glow

High quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- Vintage style, modern LED technology

PHILIPS

Highlights

WarmGlow dimming



With this dimmable bulb, you can dim from a 2700k warm light to a 2200K light. The more you dim, the warmer the light.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Vintage style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Specifications

Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 10.8 cm
- Weight: 0.04 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Beam angle: 300 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700-2200 K
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 85 mA
- Mercury content: 0 mg
- Efficacy: 100 lm/W

Packaging information

- EAN: 046677469740
- EOC: 469742
- Product title: 8A19/PER/927-922/CL/G/E26/WGX4/2BBT20

Power consumption

- Power factor: 0.75
- Voltage: 120 V
- Wattage: 8 W
- Wattage equivalent: 60 W

Rated values

- Rated beam angle: 300 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800 lumen
- Rated power: 8 W

Packaging dimensions and weight**[8.5A19/AMB/822-27/E26/CL/GL/WGD 2BC CA]**

- EAN/UPC - product: 046677469740
- Net weight: 0.140 kg
- Gross weight: 0.189 kg
- Height: 20.400 cm
- Length: 6.300 cm
- Width: 20.000 cm
- Material number (12NC): 929001315635
- EAN/UPC - Case: 50046677469745
- SAP Gross Weight EAN (Piece): 0.000 kg
- Net Weight: 0.070 kg
- SAP Length (Piece): 0.000
- SAP Width (Piece): 0.000
- SAP EAN/UPC - Set: 046677469740

Packaging dimensions and weight**[8A19/PER/927-922/CL/G/E26/WGX4/2BBT20]**

- EAN/UPC - product: 046677469740
- Net weight: 0.100 kg
- Gross weight: 0.165 kg
- Height: 17.000 cm
- Length: 8.200 cm
- Width: 15.600 cm
- Material number (12NC): 929001969605
- EAN/UPC - Case: 50046677469745
- SAP Gross Weight EAN (Piece): 0.000 kg
- Net Weight: 0.050 kg
- SAP Length (Piece): 0.000
- SAP Width (Piece): 0.000
- SAP EAN/UPC - Set: 046677469740



Issue date: 2020-02-20
Version: 0.277

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com