



PHILIPS  
LED  
Reflector (Dimmable)  
5.5W (50W)  
E26  
Bright White  
Dimmable

046677470043

## Durable LED accent lighting with a focused beam

The directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps

### **Long life**

- Long life bulbs - Lasts up to 25 years

### **Choose for high quality light**

- Bright white light

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as halogen spot

# PHILIPS

**Comfortable LED light that is easy on your eyes**

- Designed for the comfort of your eyes
- No visible flicker

# Highlights

## 25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

# Specifications

## Bulb characteristics

- Shape: Reflector
- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 25,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Bright White
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

### Other characteristics

- Lamp current: 55 mA
- Mercury content: 0 mg
- Lamp current: 72 lm/W

### Power consumption

- Power factor: 0.75
- Voltage: 120 V
- Wattage: 5.5 W
- Wattage equivalent: 50 W

### Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 400 lumen
- Rated power: 5.5 W

### Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677470043
- EAN/UPC - Case: 50046677470048
- SAP Gross Weight EAN (Piece): 0.072 kg
- Net Weight (Piece): 0.046 kg
- SAP Height (Piece): 20.400 cm
- SAP Length (Piece): 5.000 cm
- SAP Width (Piece): 12.000 cm



Issue date: 2019-09-25  
Version: 0.275

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)