

PHILIPS

Spot (Dimmable)

LED

7.5W (50W)

GU5.3

White

Dimmable



046677470272



Durable LED accent lighting with a focused beam

Philips LED spots provide a focused bright beam, an exceptionally long life, and significant energy savings. This MR16 spot is the perfect replacement for a 35W halogen spot with a GU5.3 base.

Dimmable

- Dimmable

Create a warm atmosphere

- Dimmable

High quality light

- Designed for the comfort of your eyes

High color rendering [CRI > 80]

- High color rendering (CRI > 80) for vivid colors

Philips LED spots

- Durable alternative to halogen spots

Highlights

Dimmable

Create the right atmosphere with dimmable LED lighting

Dimmable

Designed to provide quality dimming to create the right ambiance for any activity, from relaxed to active atmospheres.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

High color rendering (CRI>80)



The color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural outdoor light has a CRI of 100 and is used as the standard of comparison for any other light source. The CRI of Philips LED light bulbs is always higher than 80, close to the sun's value, reflecting colors truly and naturally.

Durable alternative to halogen

The durable alternative to halogen spots, Philips LED spots can be installed and forgotten about, maintaining their beautiful light beam for years and years to come.

Specifications

Characteristics

- Shape: Spot
- Dimmable: Dimmable
- Intended use: Indoor
- Lamp shape: Spot
- Socket: GU5.3
- Base: GU5.3
- Lamp shape code: MR16
- Control: Wall dimmer ; On/off switch

Bulb dimensions

- Width: 1.99 inch
- Height: 1.91 inch

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 35 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 620 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 750 mA
- Efficacy: 82 lm/W

Power consumption

- Power factor: 0.7
- Voltage: 12 V
- Wattage: 7.5 W
- Wattage equivalent: 50 W

Product dimensions & weight

- Length: 4.85 cm

Rated values

- Rated beam angle: 35 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 620 lumen
- Rated peak intensity: 1700 cd
- Rated power: 7.5 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC – product: 046677470272
- Net weight: 0.055 kg
- Gross weight: 0.072 kg
- Height: 13.500 cm
- Length: 10.000 cm
- Width: 5.200 cm
- Material number (12NC):
929001327803



Issue date: 2023-11-08
Version: 0.529

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com