



PHILIPS  
LED  
Bulb (Dimmable)  
4.5W (60W)  
E26  
Flame  
Dimmable

046677470449

## Designed to be seen

Introducing the new Philips Vintage LED lamp family, a collection that is reminiscent of familiar incandescent bulbs. They stand out when used as a statement piece, adding a sense of nostalgia to your interior.

### **Dimmable**

- Dimmable

### **Choose for high quality light**

- Extra warm light effect

### **Light beyond illumination**

- Vintage style, modern LED technology

### **Comfortable LED light that is easy on your eyes**

- Designed for the comfort of your eyes

# PHILIPS

# Highlights

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Extra warm light (2200K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

## Vintage style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Shape: Bulb
- Dimmable: Yes
- Socket: E26

## Bulb dimensions

- Height: 106 mm
- Width: 60 mm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2200 K
- Light Color Category: Flame
- Nominal luminous flux: 300 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 40 mA
- Mercury content: 0 mg

## Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 4.5 W
- Wattage equivalent: 60 W

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 300 lumen
- Rated power: 4.5 W

## Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677470449
- EAN/UPC - Case: 50046677470444
- SAP Gross Weight EAN (Piece): 0.077 kg
- Net Weight (Piece): 0.040 kg
- SAP Height (Piece): 20.400 cm
- SAP Length (Piece): 6.300 cm
- SAP Width (Piece): 14.400 cm



Issue date: 2019-04-22  
Version: 0.270

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)