



PHILIPS
LED
Candle
3W (25W)
E26
Flame
Non-dimmable

046677470531

Designed to be seen

Familiar shapes you know and love with a vintage filament look. They use around 80% less energy than traditional light bulbs thanks to the latest LED energy-saving technology, and last ten times longer.

Application areas

- Perfect for general room lighting

Long life

- Long Life

Saves up to 80% energy

- Saves up to 80% energy

Instant on

- Instant on

Vintage style, modern LED technology

- Vintage style, modern LED technology

PHILIPS

Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes

Highlights

Perfect for general room light

Modern lighting with Philips LED standard bulbs for use in table lamps, floor lamps and pendant fixtures. Ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

Long Life



Reduce the hassle of replacing bulbs so often

Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Vintage style, modern LED tech

Vintage LED bulbs are based on standard LED energy-saving technology, except the LEDs are arranged in such a way as to mimic classic incandescent bulbs. Now you can enjoy this retro-style bulb with state-of-the-art technology.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Shape: Candle
- Dimmable: No
- Base: Medium Screw base
- Lamp shape code: A15

Bulb dimensions

- Width: 1.85 inch
- Height: 3.23 inch

Durability

- Average life (at 2.7 hrs/day): 13.78 year(s)
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Application: Accent light
- Color rendering index (CRI): 80
- Color temperature: 2200 K
- Light Color Category: Flame
- Nominal luminous flux: 200 lumen

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Mercury content: 0 mg

Power consumption

- Energy Star Certified: No
- Power consumption per 1000h: 3 kW
- Voltage: 120 V
- Wattage: 3 W
- Wattage equivalent: 25 W

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677470531
- EAN/UPC - Case: 50046677470536
- SAP Gross Weight EAN (Piece): 0.036 kg
- Net Weight (Piece): 0.014 kg
- SAP Height (Piece): 20.400 cm
- SAP Length (Piece): 4.800 cm
- SAP Width (Piece): 12.000 cm



Issue date: 2019-09-18
Version: 0.270

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com