

# PHILIPS

Candle

LED

3W (25W)

E26

Flame

Non-dimmable

046677470531



## Designed to be seen

Familiar shapes you know and love with a vintage filament look. They use around 80% less energy than traditional light bulbs thanks to the latest LED energy-saving technology, and last ten times longer.

### Application areas

- Perfect for general room lighting

### Long life

- Long Life

### High quality light

- Designed for the comfort of your eyes

### Saves up to 80% energy

- Saves up to 80% energy

### Instant on

- Instant on

### Vintage style, modern LED technology

- Vintage style, modern LED technology

# Highlights

## Perfect for general room light

Modern lighting with Philips LED standard bulbs for use in table lamps, floor lamps and pendant fixtures. Ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

## Long Life



Reduce the hassle of replacing bulbs so often

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

## Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

## Vintage style, modern LED tech

Vintage LED bulbs are based on standard LED energy-saving technology, except the LEDs are arranged in such a way as to mimic classic incandescent bulbs. Now you can enjoy this retro-style bulb with state-of-the-art technology.

# Specifications

## Characteristics

- Shape: Candle
- Dimmable: No
- Base: Medium Screw base
- Lamp shape code: A15

## Bulb dimensions

- Width: 1.85 inch
- Height: 3.23 inch

#### **Durability**

- Average life (at 2.7 hrs/day): 13.78 year(s)
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

#### **Light characteristics**

- Application: Accent light
- Color rendering index (CRI): 80
- Color temperature: 2200 K
- Light Color Category: Flame
- Nominal luminous flux: 200 lumen

#### **Miscellaneous**

- EyeComfort: Yes

#### **Power consumption**

- Energy Star Certified: No
- Voltage: 120 V
- Wattage: 3 W
- Wattage equivalent: 25 W



Issue date: 2023-11-08  
Version: 0.528

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)