



PHILIPS
LED
Candle (Dimmable)
4.5W (40W)
E12
Flame
Dimmable

046677470562

Designed to be seen

Introducing the new Philips Vintage LED lamp family, a collection that is reminiscent of familiar incandescent bulbs. They stand out when used as a statement piece, adding a sense of nostalgia to your interior.

High quality light

- Designed for the comfort of your eyes

Choose for high quality light

- Extra warm light effect

Choose a simple replacement for your old bulbs

- Similar shape and size as an incandescent candle

Light beyond illumination

- Vintage style, modern LED technology

PHILIPS

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Extra warm light (2200K)

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

Vintage style, modern LED

LED Classic bulbs are based on standard LED energy-saving technology. Now you can enjoy a retro-style bulb with state-of-the-art technology combined with vintage design.

Replaces candle incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, energy-saving, standard LED candle. The perfect sustainable replacement for traditional incandescent candles.

Specifications

Bulb characteristics

- Shape: Candle
- Dimmable: Yes
- Socket: E12
- Lamp shape code: BA11

Bulb dimensions

- Height: 11.1 cm
- Width: 3.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2200 K
- Light Color Category: Flame
- Nominal luminous flux: 300 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 40 mA
- Mercury content: 0 mg

Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage: 4.5 W
- Wattage equivalent: 40 W

Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 300 lumen
- Rated power: 4.5 W

Packaging dimensions and weight

- EAN/UPC - product: 046677470562
- Net weight: 0.014 kg
- Gross weight: 0.036 kg
- Height: 20.400 cm
- Length: 3.600 cm
- Width: 12.000 cm
- SAP EAN/UPC - Piece: 046677470562
- Material number (12NC): 929001334735
- EAN/UPC - Case: 50046677470567
- SAP Gross Weight EAN (Piece): 0.036 kg
- Net Weight: 0.014 kg
- SAP Height (Piece): 20.400 cm
- SAP Length (Piece): 3.600 cm
- SAP Width (Piece): 12.000 cm



Issue date: 2020-03-02
Version: 0.462

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com