

PHILIPS

Reflector
(Dimmable)

LED

7 W (50 W)

E26

White

Dimmable

046677471163



Durable LED accent lighting with a focused beam

This directional LED bulb provides a focused beam of dimmable bright white light and is an excellent replacement for traditional reflector bulbs.

Easy to use

- Instant on

Long life

- Long Life

Dimmable

- Dimmable

Create a warm atmosphere

- Dimmable

High quality light

- Designed for the comfort of your eyes

Energy savings

- Energy savings

Highlights

Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Long Life



Reduce the hassle of replacing bulbs so often

Dimmable

Create the right atmosphere with dimmable LED lighting

Dimmable

Designed to provide quality dimming to create the right ambiance for any activity, from relaxed to active atmospheres.

Energy saving

Enjoy the energy-savings of LEDs without sacrificing light quality

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Characteristics

- Shape: Reflector
- Dimmable: Dimmable
- Intended use: Indoor
- Lamp shape: Reflector
- Base: E26
- Lamp shape code: PAR20
- Control: Wall dimmer ; On/off switch

Bulb dimensions

- Width: 2.48 inch
- Height: 3.37 inch

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 25,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 40 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 500 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 70 mA

Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 7 W
- Wattage equivalent: 50 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 500 lumen
- Rated peak intensity: 1000 cd
- Rated power: 7 W

Packaging dimensions and weight

- EAN/UPC – product: 046677471163
- Net weight: 0.135 kg
- Gross weight: 0.166 kg
- Height: 20.400 cm
- Length: 6.400 cm
- Width: 12.000 cm
- Material number (12NC):
929001316903



Issue date: 2023-11-08
Version: 0.524

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com