

PHILIPS

Reflector
(Dimmable)

LED

7 W (50 W)

E26

Soft White

Dimmable

046677471248



Durable LED accent lighting with a focused beam

The directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps

Long life

- Long life bulbs - Lasts up to 25 years

High quality light

- Designed for the comfort of your eyes

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen spot

Light beyond illumination

- Dims to a warm glow

Highlights

25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

WarmGlow dimming



With this dimmable bulb, you can dim from a 2700k warm light to a 2200K light. The more you dim, the warmer the light.

Specifications

Characteristics

- Shape: Reflector
- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 8.55 cm
- Width: 6.3 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 25,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200–2700 K
- Light Color Category: Soft White
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 70 mA
- Efficacy: 71 lm/W

Power consumption

- Power factor: 0.75
- Voltage: 120 V
- Wattage: 7 W
- Wattage equivalent: 50 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 500 lumen
- Rated power: 7 W



Issue date: 2023-11-08
Version: 0.453

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com