



PHILIPS  
LED  
Reflector (Dimmable)  
10W (75W)  
E26  
Bright White  
Dimmable



046677471286

## Durable LED accent lighting with a focused beam

The directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps

### **Long life**

- Long life bulbs - Lasts up to 25 years

### **Choose for high quality light**

- Bright white light

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as halogen spot

# PHILIPS

# Highlights

## 25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

## Bulb dimensions

- Height: 93 mm
- Weight: 0.236 kg
- Width: 94 mm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 25,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Bright White
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 86 mA
- Mercury content: 0 mg
- Lamp current: 85 lm/W

## Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 75 W

## Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 850 lumen
- Rated power: E26 W

## Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677471286
- EAN/UPC - Case: 50046677471281
- SAP Gross Weight EAN (Piece): 0.291 kg
- Net Weight (Piece): 0.255 kg
- SAP Height (Piece): 20.400 cm
- SAP Length (Piece): 9.900 cm
- SAP Width (Piece): 14.400 cm



Issue date: 2019-10-14  
Version: 0.330

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)