

PHILIPS

Reflector
(Dimmable)

LED

10W (75W)

E26

Daylight

Dimmable



046677471293



Durable LED accent lighting with a focused beam

The directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps

Long life

- Long life bulbs - Lasts up to 25 years

High quality light

- Designed for the comfort of your eyes
- Natural day light

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen spot

Highlights

25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

Natural day light



This bulb has a color temperature of 5000K, creating a lighting effect that is very close to that of natural daylight. Natural daylight helps with focus and making details easier to see.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

Specifications

Characteristics

- Shape: Reflector
- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 25,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 86 mA
- Efficacy: 85 lm/W

Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 75 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 850 lumen
- Rated power: 10 W



Issue date: 2023-11-08
Version: 0.456

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com