



PHILIPS  
LED  
Linear tube  
10.5W (26W)  
G24q/ GX24q  
Cool White  
Non-dimmable



046677472849

## Bright LED lighting with excellent light quality

This Philips LED linear tube provides an exceptionally long life and significant energy savings. With its bright colour temperature, this tube is the perfect long-lasting replacement for your linear fluorescent (TL) tubes.

### Application areas

- Perfect replacement T8 linear fluorescent application

### Plug and Play

- Plug and play

### Choose for high quality light

- Cool, white light (4000K)

# PHILIPS

**Comfortable LED light that is easy on your eyes**

- Designed for the comfort of your eyes

# Highlights

## Similar to linear fluorescents

The perfect quick and easy replacement for T8 linear fluorescent tubes. It fits directly into standard T8 linear fluorescent G13 sockets.

## Plug and play

Simple and quick do-it-yourself project with no wiring required and no need to replace your existing ballast.\*\*\*\*

## 4000K [LED Lamps]

Light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more cozy light, while those with a higher Kelvin value produce a cool, more energizing light.

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Shape: Tube
- Dimmable: No
- Intended use: Indoor
- Socket: G24q/ GX24q

## Bulb dimensions

- Height: 125.5 mm
- Width: 49.6 mm

## Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 50,000 hour(s)

## Light characteristics

- Color consistency: 6 SDCM
- Color rendering index (CRI): 82
- Color temperature: 4000 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1300 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 150-550 mA
- Mercury content: 0 mg

## Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10.5 W
- Wattage equivalent: 26 W

## Rated values

- Rated lifetime: 50,000 hour(s)
- Rated luminous flux: 1300 lumen
- Rated power: 10.5 W

## Packaging dimensions & weight

- SAP EAN/UPC - Piece: 046677472849
- EAN/UPC - Case: 50046677472844
- SAP Gross Weight EAN (Piece): 0.118 kg
- Net Weight (Piece): 0.090 kg
- SAP Height (Piece): 22.400 cm
- SAP Length (Piece): 12.000 cm
- SAP Width (Piece): 5.000 cm



Issue date: 2019-10-14  
Version: 0.330

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)