

PHILIPS

Motion sensor

Hue

Wireless installation

Automates your lights

Adjusts light to time of day

Mounts anywhere



046677473389



Automatically switches lights

Trigger your smart lights with movement. The battery-powered Hue motion sensor can be easily installed anywhere in your home.

Limitless possibilities

- Trigger smart lights with motion sensors
- Daylight sensor detects light
- Mount the motion sensor anywhere
- Customize motion sensor lights
- Requires a Philips Hue Bridge

Highlights

Trigger with motion sensor



Add a Philips Hue motion sensor to your smart lighting system to automatically switch your lights on when movement is detected, helping you navigate safely through your home.

Daylight sensor



The Hue Motion sensor's integrated daylight sensor detects when there is still enough daylight so that lights do not turn on until you need them. If it's still too dark, adjust the light sensitivity of the sensor in the Philips Hue app to personalize when you'd like the motion sensor to activate.

Mount anywhere



The motion sensor for Philips Hue smart lights is battery powered and completely wireless, allowing you to install anywhere inside your home. Place it on a shelf, mount it to a wall or ceiling with a single screw, or place it on any magnetic surface with the included magnet.

Customize motion sensor lights



With the Hue motion sensor, you can customize the lights that come on and their intensity depending on the time of day. During the evening, set the motion sensor to trigger gentle night lights to guide you in the dark. During the day, trigger crisp white light to flood your halls.

Requires a Philips Hue Bridge



This product requires a connection to the Hue Bridge (not included).

Specifications

Design and finishing

- Color: white
- Material: plastic

Environmental

- Operational humidity: suitable for use in indoor
- Operational temperature: 0°C - 40°C

Extra feature/accessory incl.

- Portable: Yes

Guarantee

- 2 years: Yes

Product dimensions & weight

- Height: 2.16 inch
- Length: 1.18 inch
- Net weight: 0.14 lb
- Width: 2.16 inch

Service

- Warranty: 2 year(s)

Technical specifications

- Weight: 65
- Battery type: AAA – Bar battery, pencil

The switch

- Batteries included: 2 x AAA
- IP rating: IP42
- Minimal battery lifetime: 2 year(s)
- Mounting options: freestanding, wall
- Sensor depth: 20 mm
- Sensor height: 55 mm
- Sensor width: 55 mm
- Software upgradeable: when connected to Hue bridge

What's supported

- Philips Hue App: IOS 13 and above, Android 8.0 and above
- Voice assistants: Amazon Alexa, Google Assistant, Apple HomeKit (Via Hue Bridge), Microsoft Cortana (Via Hue Bridge)

Packaging dimensions and weight

- EAN/UPC – product: 046677473389
- Net weight: 0.100 kg
- Gross weight: 0.154 kg
- Height: 16.500 cm
- Length: 5.500 cm
- Width: 8.800 cm
- Material number (12NC): 929001260762



Issue date: 2023-11-08
Version: 0.438

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com