

# PHILIPS

## Reflector

### LED

8-7-3W (65W)

Medium Screw base

SceneSwitch

Non-dimmable



046677473662



## One bulb, 3 color settings

With Philips SceneSwitch LED bulbs, you can switch light settings without switching bulbs. Flip your existing switch to change from soft white light, to daylight, to a cozy warm glow. No dimmer or additional installation is required.

### Application areas

- Application

### Long life

- Long Life

### High quality light

- Designed for the comfort of your eyes

### Saves up to 80% energy

- Saves up to 80% energy

### SceneSwitch

- SceneSwitch

### No dimmer or additional installation needed

- No dimmer or additional installation needed

# Highlights

## Application

Ideal for any room in your home.

## Long Life



Reduce the hassle of replacing bulbs so often

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Saves up to 80% energy



Save up to 80% energy compared to your standard bulb. It pays for itself and saves you money year after year. So reduce your energy bill and start saving Now.

## SceneSwitch

All-in-one replacement bulb that gives you three different light settings.

## No dimmer/installation needed

Delivers a variety of light scenes straight out of the box to suit your different needs and moods. The technology is in the bulb itself, so no dimmer or other additional installation is required. Simply replace your bulb with this SceneSwitch bulb, and change between different scenes at a flick of your existing wall switch.

# Specifications

## Characteristics

- Shape: Reflector
- Dimmable: No
- Intended use: Indoor
- Base: Medium Screw base
- Lamp shape code: BR30

## Bulb dimensions

- Width: 3.74 inch
- Height: 5.2 inch

## Durability

- Average life (at 2.7 hrs/day): 22.8 year(s)
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

#### Light characteristics

- Application: General light
- Color rendering index (CRI): 80
- Color temperature: 2200–2700 K
- Light Color Category: SceneSwitch
- Nominal luminous flux: 800 lumen
- Starting time: 0 s
- Warm-up time to 60% light: 0

#### Power consumption

- Energy Star Certified: Yes
- Voltage: 120 V
- Wattage: 8 W
- Wattage equivalent: 65 W

#### Rated values

- Rated lifetime: 25,000 hour(s)

#### Miscellaneous

- EyeComfort: Yes



Issue date: 2023-11-08  
Version: 0.461

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)