



PHILIPS  
LED  
Reflector (Dimmable)

10.5W (75W)  
E26  
Bright White Light Warm  
Glow  
Dimmable



046677477455

## Bright LED lighting with excellent light quality

The Philips LED WarmGlow lamps offer a new experience for dimmable LEDs, by enabling light levels to dim to the warm tones of traditional lamps. You can change the ambience from functional lighting to an inviting and cozy atmosphere.

### **Instant on**

- Instant on

### **Create the right light for your home**

- Similar shape and size as halogen reflector

### **Dims to a warm glow**

- Dims to a warm glow

# PHILIPS

**Comfortable LED light that is easy on your eyes**

- Designed for the comfort of your eyes

# Highlights

## Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

## Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

## Dims to a warm glow

As the light is dimmed, the color temperature is reduced, creating a warm glow.

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

## Bulb dimensions

- Height: 93 mm
- Weight: 0.24 kg
- Width: 94 mm

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200-30000 K
- Light Color Category: Bright White  
Light Warm Glow
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 93 mA
- Mercury content: 0 mg
- Lamp current: 80 lm/W

## Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10.5 W
- Wattage equivalent: 75 W

**Rated values**

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 850 lumen
- Rated power: 10.5 W

**Packaging dimensions & weight**

- SAP EAN/UPC - Piece: 046677477455
- EAN/UPC - Case: 50046677477450
- SAP Gross Weight EAN (Piece): 0.244 kg
- Net Weight (Piece): 0.216 kg
- SAP Height (Piece): 18.400 cm
- SAP Length (Piece): 9.800 cm
- SAP Width (Piece): 14.000 cm



Issue date: 2019-03-18  
Version: 0.272

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)