

PHILIPS

Reflector
(Dimmable)

LED

10.5W (75W)

E26

Bright White Light Warm Glow

Dimmable



046677477462



Bright LED lighting with excellent light quality

The Philips LED WarmGlow lamps offer a new experience for dimmable LEDs, by enabling light levels to dim to the warm tones of traditional lamps. You can change the ambience from functional lighting to an inviting and cozy atmosphere.

High quality light

- Designed for the comfort of your eyes

Instant on

- Instant on

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector

Dims to a warm glow

- Dims to a warm glow



Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Dims to a warm glow

As the light is dimmed, the color temperature is reduced, creating a warm glow.

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Specifications

Characteristics

- Dimmable: Dimmable
- Intended use: Indoor, Outdoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Lamp shape code: PAR30L
- Control: Wall dimmer ; On/off switch

Bulb dimensions

- Height: 11.8 cm
- Weight: 0.275 kg
- Width: 9.4 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200–30000 K
- Light Color Category: Bright White
Light Warm Glow
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 93 mA
- Efficacy: 80 lm/W

Packaging information

- Product family: Warm Glow

Power consumption

- Power factor: 0.9
- Voltage: 120 V
- Wattage: 10.5 W
- Wattage equivalent: 75 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 850 lumen
- Rated power: 10.5 W



Issue date: 2023-11-08
Version: 0.461

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com