

PHILIPS

Reflector
(Dimmable)

LED

7.5W (50W)

E26

Daylight

Dimmable



046677478575



Bright LED lighting with excellent light quality

Philips LEDspots are a perfect replacement for your halogen spot: they deliver halogen-like light and performance that you expect from the LED technology.

High quality light

- Designed for the comfort of your eyes
- Natural day light

Instant on

- Instant on

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen reflector



Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Natural day light



This bulb has a color temperature of 5000K, creating a lighting effect that is very close to that of natural daylight. Natural daylight helps with focus and making details easier to see.

Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Specifications

Characteristics

- Dimmable: Dimmable
- Intended use: Indoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Lamp shape code: PAR20
- Control: Wall dimmer ; On/off switch

Bulb dimensions

- Height: 8.55 cm
- Width: 6.3 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 25,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 70 mA
- Efficacy: 71 lm/W

Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 7 W
- Wattage equivalent: 50 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 500 lumen
- Rated power: 7 W



Issue date: 2023-11-08
Version: 0.464

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com