

PHILIPS  
LED  
Bulb (Dimmable)  
16W-100W  
E26  
Daylight  
Dimming

046677479411



## Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

### **Choose a simple replacement for your old bulbs**

- Similar shape and size as standard incandescent bulb

### **Choose for a sustainable solution**

- Long life bulbs - Lasts up to 15 years
- Saves up to 80% Energy

### **High quality LED light that lasts for decades**

- Designed for the comfort of your eyes

# PHILIPS

# Highlights

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 14 cm
- Weight: 0.105 kg
- Width: 7.8 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 250 degree(s)
- Color consistency: 4SDCM
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 1600 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 145 mA
- Mercury content: 0 mg
- Efficacy: 100 lm/W

**Packaging information**

- EAN: 046677479411
- EOC: 479410
- Product title:  
16A21/PER/950/P/E26/DIM 4/1BC  
T20

**Power consumption**

- Power factor: >0.7
- Voltage: 120 V
- Wattage: 16 W
- Wattage equivalent: 100 W

**Rated values**

- Rated beam angle: 250 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 1600 lumen
- Rated power: 16 W

**Packaging dimensions and weight**

- EAN/UPC - product: 046677479411
- Net weight: 0.058 kg
- Gross weight: 0.091 kg
- Height: 22.400 cm
- Length: 7.800 cm
- Width: 15.500 cm
- SAP EAN/UPC - Piece: 046677479411
- Material number (12NC):  
929002037105
- EAN/UPC - Case: 50046677479416
- SAP Gross Weight EAN (Piece): 0.091  
kg
- Net Weight: 0.058 kg
- SAP Height (Piece): 22.400 cm
- SAP Length (Piece): 7.800 cm
- SAP Width (Piece): 15.500 cm



Issue date: 2020-02-20  
Version: 0.193

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)