



PHILIPS
LED
Linear tube
17W (32W)
G13
Daylight
Non-dimmable

046677479794

Simple T8 LED replacement for fluorescent tubes

Philips InstantFit LED tubes easily replace fluorescent T8 lamps operated on electronic ballasts. This glass LED tube has a look and feel similar to fluorescent. This InstantFit tube has a bright white light and long lifetime.

Instant on

- Instant light when switched on

Choose for high quality light

- Natural day light

Choose a simple replacement for your old bulbs

- No UV or InfraRed

PHILIPS

Highlights

Instant On



No need to wait: Philips LED light bulbs provide their full level of brightness immediately when they are switched on. Just by flipping the switch, your room is at full brightness. There is no slow starting or waiting.

Natural day light



This bulb has a color temperature of 5000K, creating a lighting effect that is very close to that of natural daylight. Natural daylight helps with focus and making details easier to see.

No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

Specifications

Bulb characteristics

- Shape: Tube
- Dimmable: No
- Intended use: Indoor
- Socket: G13
- Technology: LED

Bulb dimensions

- Height: 1,212.3 mm
- Weight: 0.2 kg
- Width: 27.8 mm

Durability

- Average life (at 2.7 hrs/day): 37 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 36,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 80-260 mA
- Mercury content: 0 mg
- Lamp current: 123 lm/W

Power consumption

- Power factor: >0.9
- Voltage: 120 - 277 V
- Wattage: 17 W
- Wattage equivalent: 32 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 36,000 hour(s)
- Rated luminous flux: 2100 lumen
- Rated power: 17 W

Packaging dimensions & weight

- EAN/UPC - Case: 50046677479799
- SAP Gross Weight EAN (Piece): 0.000 kg
- Net Weight (Piece): 0.209 kg
- SAP Length (Piece): 0.000
- SAP Width (Piece): 0.000



Issue date: 2019-04-10
Version: 0.270

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com