



PHILIPS
LED
Reflector (Dimmable)

12W (90W)
E26
Bright White
Dimmable



046677530020



Bright LED lighting with excellent light quality

Philips LEDspots are a perfect replacement for your halogen spot: they deliver halogen-like light and performance that you expect from the LED technology.

Instant on

- Instant on

Choose for high quality light

- Bright white light

Create the right light for your home

- Similar shape and size as halogen reflector

Comfortable LED light that is easy on your eyes

- Designed for the comfort of your eyes

PHILIPS

Highlights

Instant on



Just by flipping the switch, your room is at full brightness. No slow starting or waiting.

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

Replaces halogen spot



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED reflector. The perfect sustainable replacement for traditional halogen reflectors.

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambiance for your home.

Specifications

Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 134 mm
- Weight: 0.394 kg
- Width: 122 mm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 25,000

Light characteristics

- Beam angle: 40 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Bright White
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 112 mA
- Mercury content: 0 mg
- Lamp current: 75 lm/W

Power consumption

- Power factor: 0.8
- Voltage: 120 V
- Wattage: 12 W
- Wattage equivalent: 90 W

Rated values

- Rated beam angle: 40 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 900 lumen
- Rated power: 12 W

Packaging dimensions & weight

- EAN/UPC - Case: 50046677530025
- SAP Gross Weight EAN (Piece): 0.000 kg
- Net Weight (Piece): 0.390 kg
- SAP Length (Piece): 0.000
- SAP Width (Piece): 0.000



Issue date: 2019-03-18
Version: 0.288

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com