

# PHILIPS

## Wireless dimming kit E26

Hue White

1 x E26 bulb

Warm white light

Dimmer switch included

Wireless dimming



046677530358



## Wireless dimming

Get started with the Philips Hue wireless dimming kit and enjoy smooth wireless dimming. It works out of the box. Control the bulb with the included dimmer switch, or connect everything to the Hue bridge for control from your smart device.

### Limitless possibilities

- Brighten and dim your smart lights
- Expand to a smart light system with the Hue Bridge
- Mount the dimmer switch anywhere
- Connect up to 10 smart lights




# Highlights

## Brighten and dim your lights



The Philips Hue Dimmer switch allows you to wirelessly turn your lights up high or down low.

## Expand with Hue Bridge



When connected to a Hue Bridge (\*sold separately), your smart lights become even more versatile. Control your lights from anywhere inside and outside your home using just the Philips Hue app. Set timers, routines, and add or remove lights from your system.

## Mount anywhere



The Philips Hue Dimmer switch functions as a normal wall switch and dimmer • but better. In addition to mounting with screws or strong adhesive tape, you can remove the magnetic control and carry it with you anywhere.

## Connect up to 10 smart lights



With the Philips Hue wireless dimming kit for smart lights, you can connect up to 10 lights to control simultaneously from a single dimmer switch.

# Specifications

## Bulb dimensions

- Dimensions (WxHxD): 113\*62

## Environmental

- Operational humidity: 5% <H<95% (non condensing)
- Operational temperature: -10°C – 45°C

## Guarantee

- 2 years: Yes

## Power consumption

- Energy Efficiency Label (EEL): Not applicable

## Service

- Warranty: 3 year(s)

## Technical specifications

- Weight: 78
- Bulb technology: LED

### The bulb

- Color temperature: 2700K
- Energy efficiency label: Not applicable
- Fitting: E26 screw base fitting
- Form factor: A19
- Input voltage: 110V-130V
- Lifetime: 25,000 hour(s)
- Light output: Warm white light
- Lumen output: 800 lm
- Max. operation power: 9.5 W
- Max. standby power: 0.5 W
- Number of switching cycles: 50,000
- Power factor: >0.7
- Rated lifetime: 25,000 hour(s)
- Software upgradable: when connected to Hue bridge
- Start up: Instant 100% light output
- Wattage: 9.5 W
- Wattage equivalent: 60 W
- Height: 4.2 inch
- Width: 2.4 inch
- Communication protocol: Zigbee
- Software upgradable: When connected to Hue Bridge

### The switch

- Batteries included: 1 x CR2450
- Frequency band: 2400 – 2483.5 MHz
- IP rating: 20
- Lifetime: 50000 clicks
- Max. lights per switch: 10 if not linked to Hue bridge
- Minimal battery lifetime: 3 year(s)
- Mounting options: freestanding
- Special features: Not applicable
- Weight including wall plate: 67 g
- Weight of switch: 37 g
- Zigbee Light link: IEEE 802.15.4 Protocol
- Minimal range indoor: 500 inch
- Switch depth: 0.43 inch
- Switch height: 3.6 inch
- Switch width: 1.38 inch
- Wall plate depth: 0.55 inch
- Wall plate height: 2.76 inch
- Wall plate width: 4.5 inch

### What's in the box

- Hue bulbs: 1
- Hue dimmer switch: 1

### What's supported

- HomeKit compatible: Yes
- IOS: 7 or later
- Philips Hue App: Android 7.0 and later
- Voice assistants: Amazon Alexa

### Packaging dimensions and weight

- EAN/UPC – product: 046677530358
- Net weight: 0.180 kg
- Gross weight: 0.292 kg
- Height: 16.500 cm
- Length: 7.500 cm
- Width: 17.600 cm
- Material number (12NC): 929001136991



Issue date: 2023-11-08  
Version: 0.444

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)