

PHILIPS

Linear tube
(Dimmable)

LED

24W (54W)

G5

Warm White

Dimmable

046677534165



Simple T5 LED replacement for fluorescent tubes

Philips InstantFit LED tubes replace fluorescent T5 high-output tubes operated on electronic ballasts, no rewiring needed. This plastic InstantFit tube has a bright white light, extra brightness, and a long lifetime.

High quality light

- Bright white light

Instant on

- Instant light when switched on

Plug and Play

- Plug and play

Highlights

Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

Instant On



No need to wait: Philips LED light bulbs provide their full level of brightness immediately when they are switched on. Just by flipping the switch, your room is at full brightness. There is no slow starting or waiting.

Plug and play

Simple and quick do-it-yourself project with no wiring required and no need to replace your existing ballast.****

Specifications

Characteristics

- Shape: Tube
- Dimmable: Dimmable
- Intended use: Indoor
- Lamp shape: Linear tube
- Socket: E26
- Technology: LED
- Lamp shape code: T5
- Control: On/off switch ; dimmer

Bulb dimensions

- Height: 116.2 cm
- Weight: 0.175 kg
- Width: 1.58 cm

Durability

- Average life (at 2.7 hrs/day): 51 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 50,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting
- Beam angle: 40 degree(s)
- Color rendering index (CRI): 82
- Color temperature: 3000 K
- Light Color Category: Cool White
- Nominal luminous flux: 3300 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 400-600 mA
- Efficacy: 137 lm/W

Packaging information

- Product family: InstantFit

Power consumption

- Power factor: 0.9
- Wattage: 24 W
- Wattage equivalent: 54 W

Product dimensions & weight

- Length: 116.2 cm

Rated values

- Rated beam angle: 160 degree(s)
- Rated lifetime: 50,000 hour(s)
- Rated luminous flux: 3300 lumen
- Rated power: 24 W

Technical specifications

- Frequency: 40-80 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677534165
- Net weight: 0.215 kg
- Gross weight: 0.289 kg
- Height: 119.600 cm
- Length: 2.400 cm
- Width: 2.400 cm
- Material number (12NC):
929001283703



Issue date: 2022-01-20
Version: 0.405

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com