

PHILIPS

Reflector

LED

10W-90W

E26

Bright White

Works with any existing switch

SceneSwitch

PHILIPS

LED Bulb

1 bulb, 4 color settings

90W replacement 10W LED

Indoor/Outdoor PAR38 Flood

Brightness 900 lumens

Estimated Energy Cost \$1.21 per year

046677541132



Durable LED accent lighting with a focused beam

The directional LED lamp provides a focused beam of dynamic colorful and white light and is an excellent replacement for traditional reflector lamps

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen spot

Choose for a sustainable solution

- No UV or InfraRed

Light beyond illumination

- A simple LED for everyday use

Highlights

Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Specifications

Characteristics

- Dimmable: Step dim
- Intended use: Indoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Lamp shape code: PAR38
- Control: Change color via switch

Bulb dimensions

- Height: 13.4 cm
- Weight: 0.41 kg
- Width: 12.2 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 35 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 900 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 130 mA
- Efficacy: 90 lm/W

Packaging information

- Product family: SceneSwitch
- EAN: 046677541132
- EOC: 541136
- Product title: 10PAR38/LED/830-R-G-B/F35/SSCC/G 4/1FB

Power consumption

- Power factor: 0.6
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 90 W

Product dimensions & weight

- Length: 13.4 cm

Rated values

- Rated beam angle: 35 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 2300 cd
- Rated power: 10 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677541132
- Net weight: 0.385 kg
- Gross weight: 0.482 kg
- Height: 13.700 cm
- Length: 12.500 cm
- Width: 12.500 cm
- Material number (12NC):
929001974433



Issue date: 2021-06-03
Version: 0.399

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com