

# PHILIPS

Reflector

LED

10W-90W

E26

Bright White

Works with any existing switch

SceneSwitch

PHILIPS  
LED Bulb  
1 bulb, 4 color settings  
90W replacement\*  
10W LED  
Indoor/Outdoor  
PAR38 Flood  
Brightness  
900 lumens  
Estimated Energy Cost  
\$1.21 per year  
LED

046677541132



## Durable LED accent lighting with a focused beam

The directional LED lamp provides a focused beam of dynamic colorful and white light and is an excellent replacement for traditional reflector lamps

### Choose a simple replacement for your old bulbs

- Similar shape and size as halogen spot

### Choose for a sustainable solution

- No UV or InfraRed

### Light beyond illumination

- A simple LED for everyday use

# Highlights

## Replaces halogen reflector



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting, LED capsule. The perfect sustainable replacement for traditional halogen spots.

## No UV or IR



The light has no infra-red component, so no heat is radiated. Also, there is no ultra-violet component in this light. These two characteristics mean that this light will not cause fabric and other items to fade.

## A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

# Specifications

## Bulb characteristics

- Dimmable: Step dim
- Intended use: Indoor
- Lamp shape: Reflector
- Socket: E26
- Technology: LED
- Lamp shape code: PAR38
- Control: Change color via switch

## Bulb dimensions

- Height: 13.4 cm
- Weight: 0.41 kg
- Width: 12.2 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Application: Task lighting, Accent lighting
- Beam angle: 35 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 900 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: instant full light

## Other characteristics

- Lamp current: 130 mA
- Efficacy: 90 lm/W

## Packaging information

- Product family: SceneSwitch
- EAN: 046677541132
- EOC: 541136
- Product title: 10PAR38/LED/830-R-G-B/F35/SSCC/G 4/1FB

## Power consumption

- Power factor: 0.6
- Voltage: 120 V
- Wattage: 10 W
- Wattage equivalent: 90 W

#### Product dimensions & weight

- Length: 13.4 cm

#### Rated values

- Rated beam angle: 35 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated peak intensity: 2300 cd
- Rated power: 10 W

#### Technical specifications

- Frequency: 50-60 Hz



Issue date: 2023-11-08  
Version: 0.407

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)